

# **ALLOY WHEEL BASECOAT**

## **ProWheel Alloy Wheel Basecoat**

ProWHEEL Basecoat is a specially formulated OEM basecoat for the refurbishment of alloy wheels.

- 20 most popular wheel colour
- Specialised metallic pigments to give chrome effects
- Fast drying

## Suitable substrates

Apply over either PROWSGBU or PROWSGU depending upon finish.

### Colours

PROWS01 Anthracite PROWS02 Audi Anthracite PROWS03 Audi Carbon PROWS04 Audi Chrome BMW Space Grey PROWS05 Daihatsu Silver PROWS06 PROWS07 Dutch Silver Felgin Silver PROWS08 Ferric Grey PROWS10 Ford Chrome PROWS11 Glitter Silver Himalayan Grey PROWS12 PROWS13 Land Rover Grey Sparkle Mercury Chrome PROWS14 PROWS15 Metallic Nissan Silver Peugeot Silver Porsche Anthracite PROWS17 PROWS18 PROWS19 Sparkle Silver PROWS20 Steingrau

VOC 400ml

# Application Data



Shake aerosol for at least two minutes, after agitator ball is



Apply 3-4 light cross coats from distance of 250mm from object.



5 minutes.
Touch dry
10-25 minute

5 minutes.



aerosol upsid down and empty valve.

scroll down to continue





# **ALLOY WHEEL BASECOAT**

## **Technical Data**

Chemical base Polyester resin combination

 $\begin{array}{ll} \text{VOC content} & 338 \text{ g/400ml} \\ \text{Coverage} & 0.6-0.8 \text{ m}^2 \end{array}$ 

Storage notes 10 years in appropriate

storage (-10°-25°C, relative air humidity

of max. 60%)

### Environmentally sound:

The products supplied by ProXL are 100% free of heavy metals and the caps and packaging are made of recyclable material.

### Disposal:

Completely emptied cans should be put in recycling skips or appropriate container. Cans which are not empty should be disposed off as special refuse.

This application and technical information is given to the best of our knowledge. The notes mentioned herein are, however, non-binding and do not exempt you from own tests to see whether the products supplied by us are suitable for your special application. The use and processing is beyond our control and therefore exclusively is the responsibility of the user.

VOC 400ml

